



# msi

MONITOR

## Prestige PS341WU



### SPECIFICATION

Panel Size	34"
Panel Resolution	5120 x 2160 (5K2K WUHD)
Refresh Rate	60Hz
Response time	8ms (GTG)
Panel Type	Nano IPS
Brightness (nits)	450 nits (TYP) VESA Certified DisplayHDR 600
Viewing Angle	178° (H) / 178° (V)
Aspect Ratio	21:9
Curvature	Flat
Contrast Ratio	1200:1 (TYP)
Active Display Area (mm)	798.648(H)x 335.664(V)
Pixel Pitch (H x V)	0.1554(H) X 0.1554(V)
Surface Treatment	Anti-glare
Display Colors	7 Billion
DCI-P3 / sRGB	98% / 100%
Video ports	1x DP(1.4) 2x HDMI (2.0) 1x Type C (DP)
USB ports	3x USB 3.2 Gen 1 Type A 1x USB 3.2 Gen 1 Type B
Audio ports	1x Mic-in 1x Headphone-out 1x Audio combo
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Control	5 Ways Joystick Navigator
Power Type	Internal Adaptor
Power Input	100~240V, 50~60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	35° ~ 35°
Adjustment (Height)	0 ~ 100mm
Dimension (W x H x D)	817.1 x 260.4 x 500.7(mm) / 32.17 x 10.25 x 19.71(in)
Weight (NW / GW)	8.2kg (18.08 lbs) / 10.3kg (22.71 lbs)
Note	Display Port: 5120 x 2160 (Up to 60Hz) HDMI: 3840 x 2160 (Up to 60Hz) Type C: 5120 x 2160 (Up to 60Hz)

### FEATURE



5K2K Ultra-Wide (5120 x 2160/ 21:9) resolution

5120 x 2160 / 21:9

Support 4K full-size window and a buffer workspace to preview the content simultaneously

Nano IPS Technology



Make sure the intensity and purity of colors while creating

DCI-P3 98% New Color Gamut Standard



Allows an accurate condition for precise editing, it reproduces the color just like what you see on the preview camera



**msi**

MONITOR

**Prestige PS341WU**

VESA Certified DisplayHDR 600



Enhance  
the  
intensity &  
purity of  
screen  
colors and  
the most  
dramatic  
immersion  
in the  
amazing  
HDR  
contents

PIP / PBP Mode



PIP/PBP  
mode  
provide a  
better  
efficiency  
for  
creators  
when need  
it

Creator OSD



Customize  
the Screen  
Profile,  
Screen  
Assistance  
and Color  
Gamut for  
creators  
with the  
most  
intuitive



**msi**

MONITOR

**Prestige PS341WU**

design

## CONNECTIONS



- |                            |                             |
|----------------------------|-----------------------------|
| 1. 1x HDMI (1.4)           | 8. 1x Headphone-out         |
| 2. 1x HDMI (1.4)           | 9. 1x Mic-in                |
| 3. 1x DisplayPort (2.0)    | 10. 2x USB 3.2 Gen 1 Type A |
| 4. 1x Type C (DP)          | 11. 1x Card Reader          |
| 5. 1x USB 3.2 Gen 1 Type B | 12. 1x Navi Key             |
| 6. 1x USB 3.2 Gen 1 Type A | 13. 1x Macro Key            |
| 7. 1x Audio combo          | 14. 1x Kensington Lock      |