LED step light





Inspiration will come in abundance once you try our LED accent step lights. Use them outdoors on your deck or on the stairs inside your home. You will be truly impressed by the effect!



Model	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
LEDSTEP002D	3 W	70 lm	285 lm	80	3000 K	120 V

Specifications

Die-cast aluminum housing
Over 50,000 hours of service life
Warm white light output
Optimized light spread
Low power consumption
Excellent color rendering
Superior light color consistency
Aesthetic profile
Dimmable

Install in standard electrical junction box Suitable for wet locations Refer to website for dimmer compatibility

Ideal operating temperature: -20° to 40° C

5-year warranty

Finish

BK BlackBR Bronze

SG Silver grey

WH White

Order example

LEDSTEP002D-WH

Dimmable LEDSTEP002D step light in a white finish

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.



LEDSTEP002D

