


Vanity light

These modern LED vanity lights can be installed in 2 directions; horizontal or vertical based on your desired lighting layout. Let your imagination go.



DRY



ADA
COMPLIANT



Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
LEDVAN003-CC-24	24"	22 W	1300 lm	1600 lm	90	2700, 3000, 3500, 4000, 5000 K	120 V
LEDVAN003-CC-32	32"	35 W	1900 lm	4000 lm	90	2700, 3000, 3500, 4000, 5000 K	120 V

Specifications

Over 50,000 hours of service life
 Warm white light output
 ADA compliant
 Superior color consistency
 Integrated dimmable driver
 Switch-selectable CCT: 2700 K/
 3000 K/3500 K/4000 K/5000 K in canopy
 Suitable for dry locations
 Refer to website for dimmer compatibility
 5-year warranty

Finish

- **BK** Black
- **CH** Chrome
- **SN** Satin Nickel

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.

Order example

LEDVAN003-CC-32CH
 LEDVAN003-CC-32 32"
 vanity light in a chrome finish

LEDVAN003-CC-24"



LEDVAN003-CC-32"

