## **LED Wall mount**









The SQS blends light functionality with an opportunity for artistic creation. Combine multiple fixtures to create infinite compositions or simply use alone, the choice is yours.







Model	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
SQS06	8 W	500 lm	750 lm	90	3000 K	120 V
SQS10	13 W	940 lm	1200 lm	90	3000 K	120 V
SQS15	22.5 W	1590 lm	2112 lm	90	3000 K	120 V

### **Specifications**

Cast aluminum construction
Fully sealed light engine
Over 50,000 hours of service life
Low profile design
Warm white light output
Superior color consistency
Integrated dimmable driver
ADA compliant
Suitable for wet locations
Refer to website for dimmer compatibility
Ideal operating temperature:
-20° to 40° C
5-year warranty

### Finish

BK BlackWH White


# Order example SQS10-BK

Dimmable 10" SQS wall mount in a black finish


### Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.

### SQS06



### SQS10



### SQS15

