



**DVP2 SAFETY GOGGLE**  
SERIES DVP  
SPECIFICATION SHEET



**PRODUCT FEATURES:**

- Ski style goggle
- Great for any scenario where eye protection would be needed
- High impact lens
- Chemical splash and dust resistant
- Dielectric can be worn in critical environments
- Anti-Fog lens standard
- Hard coated lens to prevent scratch
- 99.9% UV Protection
- OSHA compliant

**TECHNICAL DATA:**

- Lens Material: Polycarbonate
- Lens Vertical Length: 3.25"
- Lens Horizontal Length: 6.5"
- Lens Thickness: 4.8 mm
- Overall Length: 6.5"
- Overall Width: 3.25"
- Weight: 0.194 lbs.
- Lens: Hard Coated, Anti Fog, Anti-Scratch
- Nose Bridge: Rubberized
- Strap Material: Adjustable Elastic
- Strap Length: 20.75"
- Frame Material: Rubber
- Dielectric (contains no metal)
- Size: Universal
- COO: China

**STANDARDS & COMPLIANCE:**

- ANSI Z87+
- CE EN 166
- OSHA Compliant
- Dust and Chemical Splash Resistant
- High Impact Resistant

**APPLICATIONS & CARE:**

The DVP2 offers an adjustable headband, lightweight design, soft-touch rubber, and oversized lenses to provide wide and unobstructed viewing angles. The dielectric material is 100% metal free therefore the DVP2 can be worn in critical environments when needed.

DVP2 Goggle may be cleaned with soap and warm water then dried with a soft lint free cloth. One can use microfiber or a dry cloth made for eyewear to clean the lens. Do not clean with any harsh chemicals, gas, or an abrasive cleaner.



**OPTIFENSE**  
EYE PROTECTION

**DVP2 SAFETY GOGGLE**  
SERIES DVP  
SPECIFICATION SHEET

## Packaging and Logistics Information

SKU	LENS COLOR	FRAME COLOR	ANTI-FOG	CASE QTY	CASE WT	UPC
OF-DVP2-06	Clear	Black	Yes	60 PCS	19 lbs.	069165845666
OF-DVP2-05	Clear	Orange	Yes	60 PCS	19 lbs.	069165845673