



HI-VIZ SAFETY TAPE
SERIES RFT
SPECIFICATION SHEET



PRODUCT FEATURES:

- Highly visible
- Industrial grade
- Made of premium materials
- Water resistant and UV resistant
- Easy to install - Simply cut to size, peel and apply
- Strong adhesion
- Available in multiple colors

TECHNICAL DATA:

- Thickness:
 - .35 mm
- Size (WxL):
 - 2" x 75'
- Application Temperature
 - 39°F and above
- Operating Temperature Range
 - -40°F-220°F
- Water resistant
- UV Resistant
- COO: China

STANDARDS & COMPLIANCE:

- OSHA Compliant
- ADA Compliant

APPLICATIONS & CARE:

Incredibly strong, and versatile, our Hi-Viz Floor Tapes are made of premium materials for ultimate performance. Our tapes can withstand temperatures between -40 degrees F to 220 degrees F so you can feel safe in any temperature setting. The tape can easily be applied to many different surfaces such as concrete, fiberglass, metal, plastic, or wood. Simply cut to length, peel and apply. Care is easy too - simply clean with soap and water, a light disinfectant or detergent. These tapes comes in a variety of colors so you can select the tape that's right for you.



HI-VIZ SAFETY TAPE
SERIES RFT
SPECIFICATION SHEET

Packaging and Logistics Information

SKU	COLOR	SIZE (WxL)	CASE QTY	CASE WT	UPC
RFT-YBH-53	Black/Yellow Chevron Pattern	2" x 75'	72 Rolls	30 lbs.	069165846427
RFT-YH-53	Yellow	2" x 75'	72 Rolls	30 lbs.	069165846434