

UCWS006 - SPEC SHEET

500W Portable Power Station



Product Specifications

Item Number	UCWS006
Materials	Housing: ABS Screen: LCD Battery cells: Lithium-ion
Color	Black with gray accents
Rated Power	500W
Rated Capacity	444Wh.
Standard Capacity	120000mAh
AC Output	110 +/- 10% / 60Hz
Output Wave Pure sine wave	Pure sine wave
USB-A Outputs (2)	18W
USB-C Outputs (2)	PD 20W / PD 60W
Cigarette Light Output	12V-16.8V / 8A
DC5525 Output	12V-16.8V / 8A
Wireless Charging	15W
Charging Input	12-24V/80W Max
Recharge Time	5-7 hours
Operating Temperature	14°F to 104°F
Battery Shipping Classification	UN3480
Battery Shelf Life	1 year
Life Cycles	500 cycles

Cell Type	NMC 18650
Included Accessories	110V AC Wall Plug Power Adapter, 18V with MC4 Connector Cable, 12V Car Charger Cable
Product Weight	8.82 lbs.
Additional Features	LED indicator screen, multifunctional LED lights, passthrough charging (DC and USB only)
Shipping Method	Ground
Shipping Dimensions	10.75" W x 6.75" D x 6.5" H
Shipping Weight (box 1)	9.9 lbs.
Assembly Required	None
Warranty	1-year limited