

**PRODUCT DESCRIPTION**


Sheets of clear beveled Crystal are suspended from frames of Polished Chrome and allowed to drape in natural waves of light. All powered by xenon lamps, the Wave collection sparkles as light reflects from a multitude of angles.

MEASUREMENTS

DIMENSION : 26" L 5" H x 3.5" Ext
BACK PLATE : 25.75" W x 4.12" H x 1" HCO
HANGING WEIGHT : 4.62 lb

LAMPING

INPUT VOLTAGE : 120V
LUMENS : 1,500 Rated
BULB : 3 x 40W Xenon G9 , 120W Total
BULB INCLUDED : (Included)
DIMMABLE : Yes
CRI : 80+ CRI
COLOR_TEMP : 2900K

**FINISHES OPTION****GLASS**

Crystal 20

MATERIAL

Crystal, Steel

RATINGS

cETLus
Damp Location
ADA

**ADDITIONAL**

INSTALL UP/DOWN: Up
RATED LIFE 2000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | et2online.com