




PRODUCT DESCRIPTION

Sheets of clear beveled Crystal are suspended from frames of Polished Chrome and allowed to drape in natural waves of light. All powered by xenon lamps, the Wave collection sparkles as light reflects from a multitude of angles.



MEASUREMENTS

DIMENSION : 34" L 5" H x 3.5" Ext
 BACK PLATE : 33.7" W x 4.12" H x 1" HCO
 HANGING WEIGHT : 5.95 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 2,000 Rated
 BULB : 4 x 40W Xenon G9 , 160W Total
 BULB INCLUDED : (Included)
 DIMMABLE : Yes
 CRI : 80+ CRI
 COLOR_TEMP : 2900K

FINISHES OPTION

 Polished Chrome

GLASS

Crystal 20

MATERIAL

Crystal, Steel

RATINGS

cETLus
 Damp Location
 ADA



ADDITIONAL

INSTALL UP/DOWN: Up
 RATED LIFE 2000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



Contemporary
 Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | et2online.com