



Item No.	H	L1	L2	Inner	W×H×D	g
001-0.028	0.028" (0.71mm)	8	34	—	—	—
001-0.035	0.035" (0.89mm)	10	34	—	—	—
001-0.05	0.05" (1.27mm)	14	46	—	—	—
001-1/16	1/16"	13	46	—	—	—
001-5/64	5/64"	14	50	—	—	—
001-3/32	3/32"	17	56	—	—	—
001-7/64	7/64"	18	58	—	—	—
001-1/8	1/8"	20	59	—	—	—
001-9/64	9/64"	22	65	—	—	—
001-5/32	5/32"	24	68	—	—	—
001-3/16	3/16"	25	75	—	—	—
001-7/32	7/32"	27	81	—	—	—
001-1/4	1/4"	30	88	—	—	—
001-9/32	9/32"	34	95	—	—	—
001-5/16	5/16"	34	98	—	—	—
001-3/8	3/8"	37	110	—	—	—
001-7/16	7/16" (11mm)	42	118	—	—	—
001-1/2	1/2"	45	125	—	—	—
001-9/16	9/16"	55	138	—	—	—
001-5/8	5/8" (16mm)	57	153	—	—	—
001-3/4	3/4" (19mm)	70	175	—	—	—
001-7/8	7/8"	80	200	—	—	—
001-1/1	1"	95	235	—	—	—

Tool Type: Straight Type

Handle Type: L-Key

Measurement Type: Inch

Additional Information: L-Key Standard Length

Surface Treatment: Black Parkalized