



Item No.	H	L1	L2	Inner	W×H×D	g
008-1/16"	1/16"	15	79	100	100×80×55	187
008-5/64"	5/64"	17	84	100	115×85×52	308
008-3/32"	3/32"	17	92	100	115×85×52	437
008-7/64"	7/64"	19	97	100	115×85×52	633
008-1/8"	1/8"	20	102	100	141×95×58	838
008-9/64"	9/64"	23	104	100	141×95×58	1,138
008-5/32"	5/32"	25	108	100	141×95×58	1,439
008-3/16"	3/16"	28	118	100	187×99×57	2,313
008-7/32"	7/32"	30	125	100	203×115×68	3,320
008-1/4"	1/4"	32	135	100	203×115×68	4,579
008-5/16"	5/16"	36	152	50	203×115×68	4,050
008-3/8"	3/8"	40	170	25	203×115×68	3,309
008-7/16"	7/16" (11mm)	42	185	10	302×90×35	1,971
008-1/2"	1/2"	45	206	10	302×90×35	2,830
008-9/16"	9/16"	55	223	6	302×90×35	2,400
008-5/8"	5/8" (16mm)	60	250	4	347×102×43	2,245
008-3/4"	3/4" (19mm)	70	280	4	347×102×43	3,557
008-7/8"	7/8"	85	325	—	—	—
008-1"	1"	90	346	—	—	—

Tool Type: Straight Type
 Handle Type: L-Key
 Measurement Type: Inch
 Additional Information: L-Key Long Length
 Surface Treatment: Black Parkalized