



Item No.	H	L1	L2	Inner	W×H×D	g
008-1.5mm	1.5	16	79	100	100×80×55	173
008-2mm	2	17	86	100	115×85×52	308
008-2.5mm	2.5	18	94	100	115×85×52	501
008-3mm	3	20	101	100	141×95×58	774
008-4mm	4	25	110	100	141×95×58	1,491
008-5mm	5	28	120	100	187×99×57	2,547
008-5.5mm	5.5	30	127	100	203×115×68	3,297
008-6mm	6	32	133	100	203×115×68	4,056
008-7mm	7	34	145	50	203×115×68	3,058
008-8mm	8	36	154	50	203×115×68	4,180
008-9mm	9	38	163	25	203×115×68	2,858
008-10mm	10	40	172	25	203×115×68	3,689
008-12mm	12	45	206	10	302×90×35	2,550
008-14mm	14	55	225	6	302×90×35	2,322
008-17mm	17	60	250	4	347×102×43	2,561
008-19mm	19 (3/4")	70	280	4	347×102×43	3,557
008-21mm	21	80	310	—	—	—
008-22mm	22	85	325	—	—	—
008-24mm	24	90	346	—	—	—
008-26mm	26	100	366	—	—	—
008-27mm	27	100	375	—	—	—

Tool Type: Straight Type
 Handle Type: L-Key
 Measurement Type: Metric
 Additional Information: L-Key Long Length
 Surface Treatment: Black Parkalized