



Item No.	H	L1	L2	Inner	W×H×D	g
016-0.05"	0.05" (1.27mm)	75	50	50	95×75×50	74
016-1/16"	1/16"	79	50	50	95×75×50	104
016-5/64"	5/64"	84	50	50	95×75×50	154
016-3/32"	3/32"	92	50	50	110×80×47	245
016-7/64"	7/64"	97	50	50	110×80×47	333
016-1/8"	1/8"	102	50	50	110×80×47	446
016-9/64"	9/64"	104	50	50	110×80×47	577
016-5/32"	5/32"	108	50	50	136×90×53	744
016-3/16"	3/16"	118	50	50	136×90×53	1,148
016-7/32"	7/32"	125	50	50	182×94×52	1,653
016-1/4"	1/4"	135	50	50	182×94×52	2,300
016-5/16"	5/16"	152	25	25	182×94×52	2,028
016-3/8"	3/8"	170	25	25	198×110×63	3,268

Tool Type: Ball Point  
 Handle Type: L-Key  
 Measurement Type: Inch  
 Additional Information: L-Key Long Length  
 Surface Treatment: Black Parkalized