



Item No.	H	L1	L2	Inner	W×H×D	g
016-1.5mm	1.5	16	79	50	95×75×50	104
016-2mm	2	17	86	50	95×75×50	170
016-2.5mm	2.5	18	94	50	110×80×47	267
016-3mm	3	20	101	50	110×80×47	399
016-4mm	4	25	110	50	136×90×53	770
016-5mm	5	28	120	50	136×90×53	1,286
016-5.5mm	5.5	30	127	50	182×94×52	1,661
016-6mm	6	32	133	50	182×94×52	2,037
016-8mm	8	36	154	25	182×94×52	2,097
016-10mm	10	40	172	25	198×110×63	3,626
016-12mm	12	45	206	10	302×90×35	2,491
016-14mm	14	55	225	6	302×90×35	2,297
016-17mm	17	60	250	4	347×102×43	2,510
016-19mm	19 (3/4")	70	280	4	347×102×43	3,505
016-22mm	22	85	325	—	—	—

Tool Type: Ball Point
 Handle Type: L-Key
 Measurement Type: Metric
 Additional Information: L-Key Long Length
 Surface Treatment: Black Parkalized