



Item No.	H	L1	L2	L3	Inner	W×H×D	g
018L-5/64	5/64"	85	200	240	10	284×96×75	355
018L-3/32	3/32"	85	200	240	10	284×96×75	385
018L-1/8	1/8"	85	300	340	10	384×96×75	555
018L-5/32	5/32"	100	300	350	10	396×111×81	815
018L-3/16	3/16"	100	350	400	10	450×111×81	1,070
018L-1/4	1/4"	125	350	410	10	469×136×90	1,880
018L-5/16	5/16"	200	350	430	10	487×211×96	3,390
018L-3/8	3/8"	200	350	430	10	545×211×96	4,155

Tool Type:

Straight Type

Handle Type:

T-Handle

Measurement Type:

Inch

Additional Information:

T-Handle Long Length

Additional Information:

Plastic Handle