



Item No.	H	L1	L2	L3	Inner	W×H×D	g
018L-2	2	85	200	240	10	284×96×75	360
018L-2.5	2.5	85	200	240	10	284×96×75	396
018L-3	3	85	300	340	10	384×96×75	530
018L-4	4	100	300	350	10	396×111×81	825
018L-5	5	100	350	400	10	450×111×81	1,130
018L-6	6	125	350	410	10	469×136×90	1,755
018L-8	8	200	350	430	10	487×211×96	3,415
018L-10	10	200	350	430	10	545×211×96	4,410

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Metric

Additional Information: T-Handle Long Length

Additional Information: Plastic Handle