



Item No.	H	L1	L2	L3	Inner	W×H×D	g
018-5/64	5/64"	85	71	110	10	140×105×55	282
018-3/32	3/32"	85	110	150	10	187×90×70	326
018-1/8	1/8"	85	128	168	10	200×91×70	387
018-5/32	5/32"	100	130	180	10	220×106×76	595
018-3/16	3/16"	100	153	203	10	245×106×76	708
018-7/32	7/32"	125	160	220	10	284×130×85	1,170
018-1/4	1/4"	125	173	233	10	284×130×85	1,344

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Inch

Additional Information: T-Handle Standard Length

Additional Information: Plastic Handle