



Item No.	Drive	H	D	D2	B	Inner	W×H×D	g
21LB-3	□12.7	3	23.5	33	77	10	208×158×62	752
21LB-4	□12.7	4	23.5	33	77	10	208×158×62	764
21LB-5	□12.7	5	23.5	33	77	10	208×158×62	869
21LB-6	□12.7	6	23.5	33	77	10	208×158×62	947
21LB-7	□12.7	7	23.5	33	77	10	208×158×62	1,030
21LB-8	□12.7	8	23.5	33	77	10	208×158×62	1,157
21LB-10	□12.7	10	23.5	38	72	10	208×158×62	1,380
21LB-12	□12.7	12	23.5	38	72	10	208×158×62	1,670
21LB-14	□12.7	14	23.5	38	72	10	208×158×62	2,049
21LB-17	□12.7	17	25	41	69	10	208×158×62	2,785

Tool Type:

Straight Type

Socket Drive:

12.7mm (1/2")

Measurement Type:

Metric

Additional Information:

Overall Length 110mm