



Item No.	Drive	H	D	D2	B	Inner	W×H×D	g
21TB-5	□12.7	5	23.5	33	97	10	208×158×62	887
21TB-6	□12.7	6	23.5	33	97	10	208×158×62	980
21TB-7	□12.7	7	23.5	33	97	10	208×158×62	1,085
21TB-8	□12.7	8	23.5	33	97	10	208×158×62	1,234
21TB-10	□12.7	10	23.5	38	92	10	208×158×62	1,489
21TB-12	□12.7	12	23.5	38	92	10	208×158×62	1,825
21TB-14	□12.7	14	23.5	38	92	10	208×158×62	2,244
21TB-17	□12.7	17	25	41	89	10	208×158×62	3,020

Tool Type:

Taper Head

Socket Drive:

12.7mm (1/2")

Measurement Type:

Metric

Additional Information:

Overall Length 130mm