



Item No.	Drive	T	D	D2	B	B2	L	Inner	W×H×D	g
21XSB-20	□12.7	T20	23.3	33	34	8	67	10	170×68×53	752
21XSB-25	□12.7	T25	23.3	33	34	8	67	10	170×68×53	772
21XSB-30	□12.7	T30	23.3	33	34	8	67	10	170×68×53	772
21XSB-40	□12.7	T40	23.3	33	34	8	67	10	170×68×53	792
21XSB-45	□12.7	T45	23.3	33	34	8	67	10	170×68×53	792
21XSB-50	□12.7	T50	23.3	33	34	8	67	10	170×68×53	792
21XSB-55	□12.7	T55	23.3	38	34	10	72	10	170×68×53	942

Tool Type: Torx®
 Socket Drive: 12.7mm (1/2")
 Measurement Type: Torx®
 Additional Information: Standard Length