



Item No.	Drive	T	D	D2	B	B2	L	Hφ	DP	Inner
41XSB-7H	□6.35	T7	15	24	16	6.35	40	0.7	1.5	10
41XSB-8H	□6.35	T8	15	24	16	6.35	40	0.8	1.5	10
41XSB-10H	□6.35	T10	15	24	16	6.35	40	1	1.7	10
41XSB-15H	□6.35	T15	15	24	16	6.35	40	1.3	2	10
41XSB-20H	□6.35	T20	15	24	16	6.35	40	1.8	2.2	10
41XSB-25H	□6.35	T25	15	24	16	6.35	40	2.1	2.5	10
41XSB-27H	□6.35	T27	15	24	16	6.35	40	2.4	3	10
41XSB-30H	□6.35	T30	15	24	16	6.35	40	2.7	3.2	10

Tool Type: Torx®

Socket Drive: 6.35mm (1/4")

Measurement Type: Torx®

Additional Information: Overall Length 40mm

Additional Information: Borehole