



| Item No. | Drive | H  | D  | D2 | B   | W×H×D      | Inner | g     |
|----------|-------|----|----|----|-----|------------|-------|-------|
| 83TB-3   | □9.5  | 3  | 17 | 27 | 103 | 208×158×62 | 10    | 523   |
| 83TB-4   | □9.5  | 4  | 17 | 27 | 103 | 208×158×62 | 10    | 551   |
| 83TB-5   | □9.5  | 5  | 17 | 27 | 103 | 208×158×62 | 10    | 611   |
| 83TB-6   | □9.5  | 6  | 17 | 27 | 103 | 208×158×62 | 10    | 711   |
| 83TB-7   | □9.5  | 7  | 17 | 29 | 101 | 208×158×62 | 10    | 810   |
| 83TB-8   | □9.5  | 8  | 17 | 29 | 101 | 208×158×62 | 10    | 927   |
| 83TB-10  | □9.5  | 10 | 19 | 29 | 101 | 208×158×62 | 10    | 1,288 |

Tool Type:

Taper Head

Socket Drive:

9.5mm (3/8")

Measurement Type:

Metric

Additional Information:

Overall Length 130mm