



Item No.	Drive	T	D	D2	B	B2	L	Hφ	DP	Inner
83XSB-40H	□9.5	T40	17	29	19	8	48	3.2	3.3	10
83XSB-45H	□9.5	T45	17	29	19	8	48	3.5	3.7	10
83XSB-50H	□9.5	T50	17	29	19	8	48	3.9	3.8	10
83XSB-55H	□9.5	T55	19	29	22	10	51	4.9	4.8	10

Tool Type: Torx®  
 Socket Drive: 9.5mm (3/8")  
 Measurement Type: Torx®  
 Additional Information: Standard Length  
 Additional Information: Borehole