



| Item No. | Drive | T   | D  | D2 | B  | B2   | L  | Inner | W×H×D     | g   |
|----------|-------|-----|----|----|----|------|----|-------|-----------|-----|
| 83XSB-20 | □9.5  | T20 | 17 | 27 | 28 | 6.35 | 55 | 10    | 170×68×53 | 362 |
| 83XSB-25 | □9.5  | T25 | 17 | 27 | 28 | 6.35 | 55 | 10    | 170×68×53 | 372 |
| 83XSB-27 | □9.5  | T27 | 17 | 27 | 28 | 6.35 | 55 | 10    | 170×68×53 | 372 |
| 83XSB-30 | □9.5  | T30 | 17 | 27 | 38 | 6.35 | 65 | 10    | 170×68×53 | 402 |
| 83XSB-40 | □9.5  | T40 | 17 | 27 | 38 | 6.35 | 65 | 10    | 170×68×53 | 412 |
| 83XSB-45 | □9.5  | T45 | 17 | 29 | 38 | 8    | 67 | 10    | 170×68×53 | 492 |
| 83XSB-50 | □9.5  | T50 | 17 | 29 | 38 | 8    | 67 | 10    | 170×68×53 | 502 |

Tool Type: Torx®  
 Socket Drive: 9.5mm (3/8")  
 Measurement Type: Torx®  
 Additional Information: Standard Length