



Item No.	Pcs.	⊕	L	Inner	W×H×D	g
EA-02G ⊕No.1×75	10	No.1	75	10	172×119×46	1,780
EA-02G ⊕No.2×50	10	No.2	50	10	172×119×46	1,160
EA-02G ⊕No.2×75	10	No.2	75	10	172×119×46	1,700
EA-02G ⊕No.2×100	10	No.2	100	10	178×165×47	2,517
EA-02G ⊕No.2×150	10	No.2	150	5	164×100×44	1,988
EA-02G ⊕No.3×75	10	No.3	75	10	172×119×46	1,860
EA-02G ⊕No.3×100	10	No.3	100	10	178×165×47	2,607
EA-02G ⊕No.3×150	10	No.3	150	5	164×100×44	2,013

Tool Type: Cross Point
 Measurement Type: Cross Point
 Additional Information: 6.35 mm SHANK
 Additional Information: 9 & 13 mm groove
 Additional Information: Magnetized bits
 Additional Information: Gold colour plated