



Item No.	Pcs.	⊕	L	A	Inner	W×H×D	g
EA-08 ⊕ No.2×65	10	No.2	65	13	10	167×114×41	1,230
EA-08 ⊕ No.2×100	10	No.2	100	17	10	173×161×43	2,120
EA-08 ⊕ No.3×65	10	No.3	65	12	10	167×114×41	1,350
EA-08 ⊕ No.3×100	10	No.3	100	16	10	173×161×43	2,330

Tool Type:

Cross Point

Measurement Type:

Cross Point

Additional Information:

6.35 mm SHANK

Additional Information:

9 mm groove (OVERALL LENGTH : 65mm)

Additional Information:

13 mm groove (OVERALL LENGTH : 100mm)