



Item No.	T	L	Inner	W×H×D	g
EA-310 T10×65	T10	65	10	202×65×32	163
EA-310 T15×65	T15	65	10	202×65×32	187
EA-310 T20×65	T20	65	10	202×65×32	252
EA-310 T25×65	T25	65	10	202×65×32	329
EA-310 T30×65	T30	65	10	202×65×32	392

Tool Type: Torx®

Measurement Type: Torx®

Additional Information: 6.35 mm SHANK

Additional Information: 9 mm & 13mm groove

Additional Information: Torsion processing