



Item No.	T	Φ	L	Inner	W×H×D	g
EA-33S T8×75	T8	3.0	75	10	126×65×32	191
EA-33S T10×75	T10	3.6	75	10	126×65×32	191
EA-33S T15×75	T15	4.2	75	10	126×65×32	191
EA-33S T20×75	T20	4.8	75	10	126×65×32	191
EA-33S T25×75	T25	5.4	75	10	126×65×32	191
EA-33S T27×75	T27	5.9	75	10	126×65×32	191
EA-33S T30×75	T30	6.1	75	10	126×65×32	201
EA-33S T40×75	T40	7.0	75	10	126×65×32	201

Tool Type: Torx®

Measurement Type: Torx®

Additional Information: 6.35 mm SHANK

Additional Information: 9 & 13 mm groove