



Item No.	IP	$\Phi$	L	Inner	W×H×D	g
EA-33S 8IP×115	8 IP	3.2	115	10	126×65×32	141
EA-33S 10IP×115	10 IP	3.9	115	10	126×65×32	161
EA-33S 15IP×115	15 IP	4.4	115	10	126×65×32	181
EA-33S 20IP×115	20 IP	5.0	115	10	126×65×32	211
EA-33S 25IP×115	25 IP	5.6	115	10	126×65×32	261
EA-33S 27IP×115	27 IP	6.2	115	10	126×65×32	271
EA-33S 30IP×115	30 IP	6.2	115	10	126×65×32	281
EA-33S 40IP×115	40 IP	7.1	115	10	126×65×32	331

Tool Type: Torx Plus®

Measurement Type: Torx Plus®

Additional Information: 6.35 mm SHANK

Additional Information: 9 & 13 mm groove