



Item No.	T	Φ	L	HΦ	DP	Inner	W×H×D	g
EA-34 T8×75	T8	3.0	75	0.8	0.9	10	126×65×32	121
EA-34 T10×75	T10	3.6	75	1.0	1.4	10	126×65×32	131
EA-34 T15×75	T15	4.2	75	1.3	1.6	10	126×65×32	141
EA-34 T20×75	T20	4.8	75	1.8	2.0	10	126×65×32	151
EA-34 T25×75	T25	5.4	75	2.1	2.2	10	126×65×32	171
EA-34 T27×75	T27	5.9	75	2.4	2.4	10	126×65×32	181
EA-34 T30×75	T30	6.1	75	2.7	2.9	10	126×65×32	191
EA-34 T40×75	T40	7.0	75	3.2	3.4	10	126×65×32	211
EA-34 T8×115	T8	3.0	115	0.8	0.9	10	126×65×32	141
EA-34 T10×115	T10	3.6	115	1.0	1.4	10	126×65×32	161
EA-34 T15×115	T15	4.2	115	1.3	1.6	10	126×65×32	181
EA-34 T20×115	T20	4.8	115	1.8	2.0	10	126×65×32	211
EA-34 T25×115	T25	5.4	115	2.1	2.2	10	126×65×32	261
EA-34 T27×115	T27	5.9	115	2.4	2.4	10	126×65×32	271
EA-34 T30×115	T30	6.1	115	2.7	2.9	10	126×65×32	281
EA-34 T40×115	T40	7.0	115	3.2	3.4	10	126×65×32	331

Tool Type: Torx®

Measurement Type: Torx®

Additional Information: 6.35 mm SHANK

Additional Information: 9 & 13 mm groove

Additional Information: Borehole