



Item No.	H	L	Inner	W×H×D	g
EA-610C 2.5mm×100	2.5	100	10	202×65×32	163
EA-610C 3mm×100	3	100	10	202×65×32	187
EA-610C 4mm×100	4	100	10	202×65×32	252
EA-610C 5mm×100	5	100	10	202×65×32	329
EA-610C 6mm×100	6	100	10	202×65×32	392

Tool Type:

Straight Type

Measurement Type:

Metric

Additional Information:

6.35 mm SHANK

Additional Information:

9 mm groove

Additional Information:

Torsion processing

Additional Information:

Color printed