



Item No.	H	L	Inner	W×H×D	g
EA-610 2.5mm×65	2.5	65	10	202×65×32	163
EA-610 3mm×65	3	65	10	202×65×32	187
EA-610 4mm×65	4	65	10	202×65×32	252
EA-610 5mm×65	5	65	10	202×65×32	329
EA-610 6mm×65	6	65	10	202×65×32	392

Tool Type: Straight Type

Measurement Type: Metric

Additional Information: 6.35 mm SHANK

Additional Information: 9 mm groove

Additional Information: Torsion processing