



Item No.	H	Φ	L	Inner	W×H×D	g
EA-70 2.5mm×130	2.5	3.1	130	10	202×65×32	163
EA-70 3mm×130	3	3.4	130	10	202×65×32	187
EA-70 4mm×130	4	5	130	10	202×65×32	252
EA-70 5mm×130	5	6.2	130	10	202×65×32	329
EA-70 6mm×130	6	7	130	10	202×65×32	392
EA-70 2.5mm×160	2.5	3.1	160	10	202×65×32	185
EA-70 3mm×160	3	3.4	160	10	202×65×32	215
EA-70 4mm×160	4	5	160	10	202×65×32	300
EA-70 5mm×160	5	6.2	160	10	202×65×32	399
EA-70 6mm×160	6	7	160	10	202×65×32	485

Tool Type: Taper Head

Measurement Type: Metric

Additional Information: 6.35 mm SHANK

Additional Information: 9 & 13 mm groove