



Item No.	H	L1	L2	L3	Inner	W×H×D	g
EXH-2	2	85	54	94	10	161×111×71	293
EXH-2.5	2.5	85	54	94	10	161×111×71	308
EXH-3	3	85	70	110	10	161×111×71	337
EXH-4	4	100	77	127	10	193×114×77	529
EXH-5	5	100	89	139	10	193×114×77	626
EXH-6	6	125	93	153	10	193×162×90	1,055
EXH-8	8	125	95	155	10	193×162×90	1,081

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Metric

Additional Information: T-Handle Short Length

Additional Information: Plastic Handle