



Item No.	H	L1	L2	L3	Inner	W×H×D	g
EXT-2.5	2.5	85	110	150	10	205×96×75	332
EXT-3	3	85	126	167	10	205×96×75	379
EXT-4	4	100	130	180	10	226×111×81	596
EXT-5	5	100	153	203	10	226×111×81	739
EXT-6	6	125	170	233	10	283×138×87	1,273
EXT-8	8	125	184	245	10	283×138×87	1,763

Tool Type: Taper Head

Handle Type: T-Handle

Measurement Type: Metric

Additional Information: T-Handle Standard Length

Additional Information: Plastic Handle