



Item No.	T	L1	L2	B	Inner	W×H×D	g
IT-8	T8	15.5	47.6	2	30	102×79×55	102
IT-10	T10	17	51	2.5	30	102×79×55	132
IT-15	T15	18	54	3	30	102×79×55	162
IT-20	T20	19.5	57.5	3.5	30	102×79×55	222
IT-25	T25	20	60	4	30	102×79×55	312
IT-27	T27	21.5	63.5	4.5	20	102×79×55	282
IT-30	T30	23.5	70	5	20	102×79×55	342
IT-40	T40	26	76	6	20	102×79×55	642
IT-45	T45	28.5	82.5	7	20	102×79×55	782
IT-50	T50	32	95.5	8	20	102×79×55	1,142

Tool Type: Torx®
 Handle Type: L-Key
 Measurement Type: Torx®
 Additional Information: L-Key Standard Length
 Surface Treatment: Black Parkalized