



Item No.	H	L1	L2	Inner	W×H×D	g
LH-1/16	1/16"	15	79	20	162×68×35	68
LH-5/64	5/64"	17	93	20	162×68×35	88
LH-3/32	3/32"	18	108	20	162×68×35	125
LH-1/8	1/8"	20	127	20	162×68×35	230
LH-5/32	5/32"	25	140	20	162×68×35	380
LH-3/16	3/16"	28	158	20	202×65×32	595
LH-1/4	1/4"	32	178	20	226×75×32	1,180
LH-5/16	5/16"	36	198	10	226×75×32	1,035
LH-3/8	3/8"	40	222	10	250×90×38	1,665

Tool Type: Straight Type
 Handle Type: L-Key
 Measurement Type: Inch
 Additional Information: L-Key Extra Long Length