



Item No.	H	L1	L2	Inner	W×H×D	g
LH-1.5	1.5	16	9	20	162×68×35	60
LH-2	2	17	95	20	162×68×35	90
LH-2.5	2.5	18	110	20	162×68×35	140
LH-3	3	20	126	20	162×68×35	205
LH-4	4	25	142	20	162×68×35	390
LH-5	5	28	160	20	202×65×32	665
LH-6	6	32	180	20	226×75×32	1,070
LH-8	8	36	200	10	226×75×32	1,060
LH-10	10	40	224	10	250×90×38	1,845
LH-12	12	45	250	4	275×78×35	1,205
LH-14	14	55	280	4	302×90×35	1,840
LH-17	17	60	320	4	347×102×43	3,080
LH-19	19 (3/4")	70	360	4	411×96×47	4,135

Tool Type:

Straight Type

Handle Type:

L-Key

Measurement Type:

Metric

Additional Information:

L-Key Extra Long Length