



Item No.	H	L1	L2	Inner	W×H×D	g
R-0.05"	0.05"(1.27mm)	14	46	20	126×65×32	35
R-1/16	1/16"	13	46	20	126×65×32	42
R-5/64	5/64"	14	50	20	126×65×32	60
R-3/32	3/32"	17	56	20	126×65×32	80
R-7/64	7/64"	18	58	20	126×65×32	100
R-1/8	1/8"	20	59.5	20	126×65×32	130
R-9/64	9/64"	22	65	20	126×65×32	175
R-5/32	5/32"	24	68	20	126×65×32	220
R-3/16	3/16"	25	75	20	126×65×32	325
R-7/32	7/32"	27	81	20	126×65×32	470
R-1/4	1/4"	30	88.5	20	126×65×32	670
R-5/16	5/16"	34	98	10	162×68×35	600
R-3/8	3/8"	37	110	10	162×68×35	910
R-1/2	1/2"	45	125	10	162×111×44	1,935

Tool Type: Straight Type
 Handle Type: L-Key
 Measurement Type: Inch
 Additional Information: L-Key Standard Length