



Item No.	H	L1	L2	Inner	W×H×D	g
R-1.5	1.5	12	52	20	126×65×32	170
R-2	2	12	58	20	126×65×32	188
R-2.5	2.5	15	60	20	126×65×32	214
R-3	3	20	65	20	126×65×32	252
R-4	4	25	72	20	126×65×32	362
R-5	5	28	80	20	126×65×32	672
R-6	6	32	90	20	126×65×32	902
R-8	8	36	100	10	162×68×35	745
R-10	10	40	112	10	162×68×35	1,294
R-12	12	45	125	10	162×111×44	1,951
R-14	14	55	140	10	187×102×59	2,977
R-17	17	60	160	4	187×102×59	1,818
R-19	19 (3/4")	70	175	4	223×99×47	2,510

Tool Type:

Straight Type

Handle Type:

L-Key

Measurement Type:

Metric

Additional Information:

L-Key Standard Length