



Item No.	H	L1	L2	L3	Inner	W×H×D	g
ST500-3	3	80	25	500	10	544×111×50	2,403
ST500-4	4	100	35	500	10	544×111×50	2,457
ST500-5	5	120	50	500	10	544×132×59	3,810
ST500-6	6	160	50	500	10	544×169×77	5,726
ST500-8	8	180	60	500	10	544×190×93	8,215

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Metric

Additional Information: T-Handle Long Length

Additional Information: Steel Handle