



Item No.	H	L1	L2	L3	Inner	W×H×D	g
ST-2.5	2.5	80	25	190	10	205x95x70	1,085
ST-3	3	80	25	190	10	205x95x70	1,092
ST-4	4	100	35	200	10	225x110x80	1,205
ST-5	5	120	50	250	10	290x135x90	2,211
ST-6	6	160	50	250	10	325x177x67	3,508
ST-8	8	180	60	300	10	340x215x97	5,620
ST-10	10	200	25	300	10	340x215x97	4,698
ST-12	12	200	25	320	5	340x215x97	4,902
ST-14	14	200	30	320	5	340x215x97	4,338

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Metric

Additional Information: T-Handle Standard Length

Additional Information: Steel Handle