



TD-1.3~TD-2



TD-2.5~TD-1/4



TD-4 to TD-6 and TD-3/16 to TD-1/4 screwdrivers come with an L type wrench for retightening.

Item No.	H	L1	L2	Φ	Inner	W×H×D	g
TD-3/32	3/32"	90	85	18	10	238×120×46	408
TD-7/64	7/64"	95	94	21	10	259×144×56	458
TD-1/8	1/8"	100	94	21	10	259×144×56	648
TD-9/64	9/64"	100	94	21	10	290×166×65	778
TD-5/32	5/32"	125	102	26	10	290×166×65	1,078
TD-3/16	3/16"	140	109	30	5	332×132×50	843
TD-7/32	7/32"	145	109	30	5	332×132×50	938
TD-1/4	1/4"	150	109	30	5	332×132×50	1,008

Tool Type: Taper Head

Handle Type: SCREWDRIVER

Measurement Type: Inch

Additional Information: Plastic Handle