



TD-1.3~TD-2



TD-2.5~TD-1/4



TD-4 to TD-6 and TD-3/16 to TD-1/4 screwdrivers come with an L type wrench for retightening.

| Item No. | H            | L1  | L2  | Φ  | Inner | W×H×D      | g     |
|----------|--------------|-----|-----|----|-------|------------|-------|
| TD-1.3   | 1.27 (0.05") | 60  | 82  | 11 | 10    | 162×68×35  | 131   |
| TD-1.5   | 1.5          | 70  | 82  | 11 | 10    | 162×68×35  | 133   |
| TD-2     | 2            | 80  | 87  | 15 | 10    | 202×65×32  | 207   |
| TD-2.5   | 2.5          | 90  | 85  | 18 | 10    | 238×120×46 | 406   |
| TD-3     | 3            | 100 | 94  | 21 | 10    | 259×144×56 | 610   |
| TD-4     | 4            | 125 | 102 | 26 | 10    | 290×166×65 | 1,073 |
| TD-5     | 5            | 140 | 109 | 30 | 5     | 332×132×50 | 853   |
| TD-6     | 6            | 150 | 109 | 30 | 5     | 332×132×50 | 975   |

Tool Type: Taper Head  
 Handle Type: SCREWDRIVER  
 Measurement Type: Metric  
 Additional Information: Plastic Handle