



Item No.	H	L1	L2	Inner	W×H×D	g
TEL-1/16	1/16"	15	79	20	162×68×35	55
TEL-5/64	5/64"	17	93	20	162×68×35	90
TEL-3/32	3/32"	18	108	20	126×65×32	120
TEL-1/8	1/8"	20	127	20	162×68×35	220
TEL-5/32	5/32"	25	140	20	162×68×35	380
TEL-3/16	3/16"	28	158	20	202×65×32	600
TEL-1/4	1/4"	32	178	20	226×75×32	1,200
TEL-5/16	5/16"	36	198	10	226×75×32	1,025
TEL-3/8	3/8"	40	222	10	226×75×32	1,625
TL-7/16	7/16"	43	240	4	275×78×35	995
TL-1/2	1/2"	45	248	4	275×78×35	1,320
TL-9/16	9/16"	55	278	4	302×90×35	995
TL-5/8	5/8" (16mm)	60	320	4	347×102×43	2,645
TL-3/4	3/4"	70	360	4	411×96×47	4,255

Tool Type:

Taper Head

Handle Type:

L-Key

Measurement Type:

Inch

Additional Information:

L-Key Extra Long Length