



Item No.	Pcs.	H										Inner	W×H×D	g
TLC-S9NPPU	9	1.5	2	2.5	3	4	5	6	8	10	5	305×100×110	2,440	



Item No.	H	L1	L2
TLC-1.5PU	1.5	16	79
TLC-2PU	2	17	95
TLC-2.5PU	2.5	18	110
TLC-3PU	3	20	126
TLC-4PU	4	25	142
TLC-5PU	5	28	160
TLC-6PU	6	32	180
TLC-8PU	8	36	200
TLC-10PU	10	40	224



L	Aφ	Bφ
150	15.9	14.2
110	9.5	8.5

Tool Type:

Taper Head

Handle Type:

L-Key

Measurement Type:

Metric

Additional Information:

L-Key Extra Long Length

Additional Information:

Single-Color PURPLE

Additional Information:

Extension Pipes x 2 pcs.