



Item No.	H	L1	L2	Inner	W×H×D	g
014-1.5mm	1.5	16	79	20	162×68×35	50
014-2mm	2	17	95	20	162×68×35	90
014-2.5mm	2.5	18	110	20	162×68×35	130
014-3mm	3	20	126	20	162×68×35	210
014-4mm	4	25	142	20	162×68×35	390
014-5mm	5	28	160	20	202×65×32	660
014-5.5mm	5.5	30	170	20	226×75×32	1,055
014-6mm	6	32	180	20	226×75×32	1,376
014-7mm	7	34	190	10	226×75×32	2,136
014-8mm	8	36	200	10	226×75×32	995
014-9mm	9	38	220	10	250×90×38	1,190
014-10mm	10	40	224	10	250×90×38	1,815
014-12mm	12	45	250	4	275×78×35	3,025
014-14mm	14	55	280	4	302×90×35	4,255
014-17mm	17	60	320	4	347×102×43	
014-19mm19 (3/4")	70	360	4	411×96×47		

Tool Type:

Straight Type

Handle Type:

L-Key

Measurement Type:

Metric

Additional Information:

L-Key Extra Long Length

Surface Treatment:

Black Parkalized