



Item No.	T	L1	L2	BΦ	HΦ	DP	Inner	W×H×D	g
TXBH-8	T 8	17	86	2.5	0.7	1.0	10	126×68×50	60
TXBH-10	T 10	18	94	2.7	1.0	1.2	10	126×68×50	70
TXBH-15	T 15	21	99	3.3	1.3	1.6	10	126×68×50	100
TXBH-20	T 20	22	106	3.8	1.8	2.0	10	126×68×50	135
TXBH-25	T 25	25	110	4.4	2.1	2.1	10	162×68×35	185
TXBH-27	T 27	27	115	5.0	2.4	2.3	10	162×68×35	240
TXBH-30	T 30	29	123	5.5	2.7	2.5	10	162×68×35	300
TXBH-40	T 40	32	133	6.6	3.2	3.1	10	162×68×35	460

Tool Type: Torx® Ball Point

Handle Type: L-Key

Measurement Type: Torx®

Additional Information: L-Key Long Length

Additional Information: Borehole On Both Ends