



Item No.	T	L1	L2	BΦ	Φ	HΦ	DP	Inner	W×H×D	g
TXDH-6	T 6	60	69	2.5	18	0.7	1.5	20	167×94×54	336
TXDH-7	T 7	65	69	2.5	18	0.7	1.5	20	167×94×54	469
TXDH-8	T 8	70	69	2.5	18	0.7	1.5	20	167×94×54	471
TXDH-9	T 9	70	84	3.3	22	0.8	1.5	20	191×109×59	695
TXDH-10	T 10	75	84	3.3	22	1.0	1.7	20	191×109×59	703
TXDH-15	T 15	80	84	3.3	22	1.3	2.0	20	191×109×59	711
TXDH-20	T 20	90	99	4.4	26	1.8	2.2	10	227×131×33	673
TXDH-25	T 25	100	99	4.4	26	2.1	2.5	10	227×131×33	685
TXDH-30	T 30	120	122	6.6	32	2.7	3.2	10	267×158×42	1,376
TXDH-40	T 40	130	122	6.6	32	3.2	3.7	10	274×101×67	1,369

Tool Type: Torx®

Handle Type: SCREWDRIVER

Measurement Type: Torx®

Additional Information: Plastic Handle

Additional Information: Boreholed