



Item No.	T	L1	L2	BΦ	Φ	Inner	W×H×D	g
TXD-5	T5	55	70	2.5	13	20	148×65×28	308
TXD-6	T6	60	70	2.5	13	20	148×65×28	308
TXD-7	T7	65	70	2.5	13	20	148×65×28	313
TXD-8	T8	70	70	2.5	13	20	148×65×28	319
TXD-9	T9	70	78	3.3	17	20	160×80×40	507
TXD-10	T10	75	78	3.3	17	20	160×80×40	516
TXD-15	T15	80	78	3.3	17	20	160×80×40	521
TXD-20	T20	90	94	4.4	21	10	200×100×30	515
TXD-25	T25	100	94	4.4	21	10	200×100×30	528
TXD-27	T27	110	94	5.0	21	10	242×112×31	596
TXD-30	T30	120	110	6.6	24	10	242×112×31	1,008
TXD-40	T40	130	110	6.6	24	10	242×112×31	1,035

Tool Type: Torx Plus®

Handle Type: SCREWDRIVER

Measurement Type: Torx Plus®

Additional Information: Plastic Handle